

Refrigerated Heating Bath with air-cooled refrigerating unit. Consisting of isolated cooling bath made of stainless steel with immersion thermostat. Pump and wetted parts made from stainless steel or high-resistant plastics. With adjustable overtemperature protection according to DIN 12876.

**Pilot ONE:**

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

3-2-2 warranty - registration required.

**Technical data according to DIN 12876**

Operating temperature range	-25...200 °C
Temperature stability at 70°C	0,02 K
temperature set point / display	5,7" colour Touchscreen
Absolute accuracy	setup for calibration
Internal temperature sensor	Pt100
Sensor external connection	Pt100
Interface digital	Ethernet, USB (Host u. Device), RS232
Safety classification	III / FL
Heating power at 240V	2,1 kW
Heating power at 230V	2 kW
Heating power at 220V	1,8 kW
Heating power at 208V	1,6 kW
Cooling power	
at 20°C	0,2 kW
at 0°C	0,15 kW
at -10°C	0,1 kW
at -20°C	0,05 kW
Refrigeration machine	air-cooled, natural refrigerant
Kältemittel (ASHRAE, GSH)	R290 (A3, H220)
Refrigerant quantity	0,047 kg
Gas warning sensor	without
Pressure / Suction pump	
max. delivery	27 l/min
max. delivery pressure	0,7 bar
max. delivery (suction)	22 l/min
max. delivery pressure (suction)	0,4 bar
Pump connection	M16x1 male
Bath volume	4,5 l
Width bath opening WxD	140x120 mm
Bath depth	150 mm
Height of bath opening	376 mm
Overall dimensions WxDxH **	210x400x546 mm
Net weight	25 kg
sound pressure level +/- 4 dB(A)	57 dB(A)



**Order-No.: 2008.0005.01**

## Technical data according to DIN 12876

---

Power supply requirement	208-240V 1~/2~ 50/60Hz
max. current refrigerated bath	1,35 A
max. current immersion thermostat	10 A
min. Fuse	10A
max. Fuse	16A
Degree of Protection	IP20
min. ambient temperature	5 °C
max. ambient temperature	40 °C

---

**from Serial-No.:**

**393652**

**1.3/20**

---

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included accessories:

mini USB cable #54949, hose connector NW12 #6087, blank plug #6088, sleeve nuts thread #6089, bath cover #14451, data cable #9472,

Optional accessories:

drain valve , PS level regulator #9580, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20° C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)