

## Bransonic® CPX Ultrasonic Baths

### General Description

Bransonic CPX ultrasonic baths feature digital controls with power tracking capabilities to adjust for light or heavy loads, high/low power control, degassing and sleep mode.

### The CPX baths offer the following features:

- Sweep frequency eliminates standing waves and creates consistent cavitation throughout the tank.
- 40 kHz rugged industrial transducers.
- 99-minute digital timer with continuous ultrasonic operation.
- Last stored parameters are recalled when unit is turned back on.
- **Constant activity/power tracking** automatically maintains the ultrasonic power by adjusting for changes in liquid level and temperature caused by a light or heavy load. This helps ensure more uniform cleaning and consistent performance, even with multiple users or when bath conditions change.
- **Degassing and conditioning the solution:** The CPX degassing period can be set up to 99 minutes. Extended degas time periods allow for “beyond cleaning” applications such as sample preparation, which includes degassing liquids, mixing and homogenization, dissolving solids, cell lysing, and dispersion of particles.
- **High/low power control:** When cleaning delicate parts, the CPX allows the user to lower the amplitude of the acoustic energy in the bath: 100% power to the tank for normal applications, 70% power for delicate applications. Manipulating the output waveform in this manner greatly helps to avoid damage to the components in the bath during the ultrasonic process.
- Controls are located above and behind the cleaning tank in an easily accessible control tower panel, and raised above the tank to avoid damage from cleaning solutions.
- Convenient built-in pour drains are featured on .5- and .75-gallon models. Tank drains with valves are incorporated on models 1.5-gallon and larger.
- Plastic body, chemical-resistant.

Consult with your Branson representative about the Bransonic accessories and solution best suited for your application needs. **Visit us at [www.Bransonic.com](http://www.Bransonic.com)**



# BRANSON

## CPX Series (Digital timer)

Ordering Part No.	Voltage	Model 1800	Model 2800	Model 3800	Model 5800	Model 8800
	120 V	CPX1800	CPX2800	CPX3800	CPX5800	CPX8800
Part No.		CPX-952-119R	CPX-952-219R	CPX-952-319R	CPX-952-519R	CPX-952-819R
	230/240 V	CPX1800-E	CPX2800-E	CPX3800-E	CPX5800-E	CPX8800-E
Part No.		CPX-952-139R	CPX-952-239R	CPX-952-339R	CPX-952-539R	CPX-952-839R

## Specifications

	Model 1800	Model 2800	Model 3800	Model 5800	Model 8800
<b>Tank Capacity</b>					
Liters/Gallons	1.9/0.5	2.8/0.75	5.7/1.5	9.5/2.5	20.8/5.5
<b>Tank Size (L/W/D)</b>					
Inches	6 x 5.5 x 4	9.5 x 5.5 x 4	11.5 x 6 x 6	11.5 x 9.5 x 6	19.5 x 11.5 x 6
mm	150 x 140 x 100	230 x 140 x 100	290 x 150 x 150	290 x 240 x 150	495 x 290 x 150
<b>Overall Size (L/W/D)</b>					
Inches	9.9 x 12 x 11.9	13.3 x 12 x 11.9	15.6 x 12.5 x 14.8	15.6 x 15.8 x 14.9	23.5 x 18.3 x 15.4
mm	251 x 304 x 302	337 x 304 x 302	397 x 317 x 377	397 x 401 x 378	596 x 466 x 391
<b>Weight</b>					
Pounds/Kilograms	7/3.2	9/4.1	12/5.4	14/6.4	26/11.8
<b>Frequency</b>	40 kHz	40 kHz	40 kHz	40 kHz	40 kHz
<b>Drain</b>	No	No	Yes	Yes	Yes

**NOTE: Tank cover included. For optimum cleaning results, Branson offers a line of accessories including perforated trays, solid trays, beaker covers and support racks for your application needs.**

### Americas

Branson Ultrasonics Corp.  
41 Eagle Road  
Danbury, CT 06810, USA  
T: 203-796-0400  
F: 203-796-2250  
Toll Free: 800-732-9262  
www.bransonultrasonics.com

### Europe and Africa and Middle East

Branson Ultrasonic SA  
Ch. du Faubourg-de-Cruseilles 9  
1227 Carouge  
Switzerland  
T: +41(0)22 3048353  
F: +41(0)22 3048359  
www.branson.ch

### Asia

Branson Ultrasonics (Shanghai) Co., Ltd.  
758 Rong Le Dong Road  
Song Jiang, Shanghai, PRC, 201613  
T: 86-21-3781-0588  
F: 86-21-5774-5100  
www.branson.com.cn

All specifications subject to change without notice. All dimensions are nominal.  
All ultrasonic baths meet FCC, CSA, CE & UL rules and regulations.  
Standard two year warranty.



© Branson Ultrasonics Corporation 2012.  
The Emerson logo is a trademark and service mark  
of Emerson Electric Co.  
Printed in the U.S.A.

BCL-0002-12