



More information on the website  
[radwag.com/en/info,w1,MD7](http://radwag.com/en/info,w1,MD7)

### XA 52.5Y Analytical Balance



XA 52.5Y Analytical Balance

The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Autotest



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



Newton unit measurement



Statistics



Checkweighing



IR sensors



Under-pan weighing



GLP Procedures



Animal weighing



Pipettes Calibration



Air density correction



Density determination



Differential weighing



Ambient conditions monitoring



Statistical Quality Control



Packaged Goods Control



ALIBI Memory



Wi-Fi

# Datasheet

	XA 52.5Y Analytical Balance
<b>Metrological parameters</b>	
Maximum capacity [Max]	52 g
Minimum load	1 mg
Readability [d]	0,01 mg
Verification scale interval [e]	1 mg
Tare range	-52 g
Standard repeatability [5% Max]	0,005 mg
Standard repeatability [Max]	0,01 mg
Standard minimum weight (USP)	10 mg
Standard minimum weight (U=1%, k=2)	1 mg
Permissible repeatability [5% Max]	0,012 mg
Permissible repeatability [Max]	0,02 mg
Linearity	±0,03 mg
Eccentric load deviation	0,03 mg
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times R_t$
Stabilization time	4 s
Adjustment	internal (automatic)
OIML Class	I
<b>Physical parameters</b>	
Leveling system	semi-automatic - LevelSENSING
Display	10" touchscreen
Delivery components	Analytical Balance, weighing pan, weighing pan shield, centring ring, bottom cover, brush, fabric dust cover, power supply.
Weighing chamber dimensions	168×160×228 mm
Weighing pan dimensions	ø90 + ø85 (option) mm
Packaging dimensions	435 x 885 x 540 mm
Net weight	9,8 kg
Gross weight	14,3 kg
<b>Communication interface</b>	
Communication interface	USB-A ×2, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
<b>Electrical parameters</b>	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,6A max*
<b>Environmental conditions</b>	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3°C/1h (±1°C/8h)
Relative humidity	20% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

\* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories

Barcode scanners  
Density determination KIT  
Professional weighing table  
Protective cover for balances  
Holders for test tubes and filters  
USB Hubs  
Label Printers  
Holders for laboratory flasks

THBR 2.0 System - Ambient Conditions Monitoring  
Under-Pan Weighing Rack  
Anti-Draft Chamber for XA 4Y and XA 5Y Balances  
Weighing dishes  
Receipt Printer  
Fingerprint Reader  
RS 232 – USB Converter  
Under-pan weighing

## Software

RAD-KEY  
Label Editor R02  
Scales Editor 2.1  
R.Barcode

LabVIEW Driver  
RADWAG Remote Desktop  
RADWAG Development Studio

## Device dimensions

XA 52.5Y Analytical Balance

