

Data Sheet

UPLXAPO10X

ImageImageImageImageJimensionImageInquiryContact usLineX LineMajor applicationV Life ScienceMagnification [X]0Numerical aperture (NA)0.4Objective field number [mm]0.17Objective field number [mm]0.17Correction collarN/APartication [X]N/ACorrection collarN/APartication [M]1.91Correction collarN/APartocal plane (MP) position [mm]4.5Correction collarSciencealPartocalizing distance (mm]4.5Correction collarN/APartocalizing distance [mm]0.12Signified (Reflected)N/AMandel (Reflected)N/ACorrection collarScientartFignified (Reflected)N/ACorrection collarScientartFignified (Reflected)N/ACorrection collarScientartFignified (Reflected)N/ACorrection collarScientartCorrection collarScientartFignified (Reflected)N/ACorrection collarScientartCorrection collarScientartFignified (Reflected)N/ACorrection collarScientartFignified (Reflected)N/ACorrection collarScientartFignified (Reflected)N/ACorrection collarScientartFignified (Reflected)ScientartFignified	Product name	UPLXAPO10X
InquiryContact usLineX LineMajor application• Life ScienceMagnification [X]10Numerical aperture (NA)0.4Working distance (WD) [mm]3.1Objective field number [mm]26.5Cover glass thickness [nm]0.17Immersion mediumAir/DrySpring loadedN/ACorrection collarN/ACorrection collarN/APartocalizing distance [mm]45Back focal plane (BFP) position [mm]-19.1Type of screw threadN/ABrightfield (Reflected)N/ADarklield (Transmitted)ExcellentDic (Reflected)N/ADic (Reflected)N/APhase contrastN/AFunder (Transmitted)ExcellentPhase contrastN/AFunder (Transmitted)ExcellentPhase contrastN/APhase contrastN/AFunder (Transmitted)ExcellentPhase contrastN/APhase cont	Image	
LineX LineMajor application• Life ScienceMagnification [X]10Numerical aperture (NA)0.4Working distance (WD) [mm]3.1Objective field number [mm]26.5Cover glass thickness [mm]0.17Immersion mediumAir/DrySpring loadedN/ACorrection collarN/ARemarks (Correction collar)Extended Apochromat (XAPO)Parfocalizing distance [mm]45Back focal plane (BFP) position [mm]19.1Type of screw threadW20.32×0.706 (RMS)Brightield (Reflected)N/ADarkfield (Reflected)N/ADarkfield (Reflected)N/ADarkfield (Reflected)N/ADarkfield (Reflected)N/ADarkfield (Reflected)N/ADarkfield (Reflected)N/ABrightield (Reflected)N/ADarkfield (Reflected)N/ABrightield (Reflected)N/ABrightield (Reflected)N/ABrightield (Reflected)N/ABrightield (Reflected)N/ADarkfield (Reflected)N/ADarkfield (Reflected)N/ABrightield (Reflected)N/ADarkfield (Reflected)N/ABrightield (Reflected)N/ABrightield (Reflected)N/ABrightield (Reflected)N/ABrightield (Reflected)N/ABrightield (Reflected)N/ABrightield (Reflected)N/ABrightield (Reflected)N/ABrightield (Reflect	Dimension	
Major application. Life ScienceMagnification [X]10Numerical aperture (NA)0.4Working distance (WD) [mm]3.1Objective field number [mm]26.5Cover glass thickness [mm]0.17Immersion mediumAir/DrySpring loadedN/ACorrection collarN/ARemarks (Correction collar)VI/ACorrection level of chromatic aberrationExtended Apochromat (XAPO)Parfocalizing distance [mm]45Back focal plane (BFP) position [mm]-19.1Type of screw threadW20.32×0.706 (RMS)Brightfield (Transmitted)GoodDarkfield (Transmitted)GoodDirkfield (Transmitted)N/ADirkfield (Transmitted)N/ADirkfield (Transmitted)N/ADirkfield (Transmitted)N/ADirkfield (Transmitted)N/ADirkfield (Transmitted)N/ABightfield Transmitted)N/ADirkfield Transmitted)N/ADirkfield (Transmitted)N/ADirkfield (Transmitted)N/ADirkfield Transmitted)N/ADirkfield T	Inquiry	Contact us
Magnification [X]10Numerical aperture (NA)0.4Working distance (WD) [mm]3.1Objective field number [mm]26.5Cover glass thickness [mm]0.17Immersion mediumAir/DrySpring loadedN/ACorrection collarN/ARemarks (Correction collar)V/AIrisN/ACorrection level of chromatic aberrationExtended Apochromat (XAPO)Parfocalizing distance [mm]45Back focal plane (BFP) position [mm]-19.1Type of screw threadW20.32×0.706 (RMS)Brightfield (Transmitted)ExcellentDarkfield (Reflected)N/ADic (Reflected)N/ADic (Transmitted)ExcellentPhase contrastN/AFueler contrastN/A	Line	X Line
Numerical aperture (NA)0.4Working distance (WD) [mm]3.1Working distance (WD) [mm]26.5Cover glass thickness [mm]0.17Immersion mediumAir/DrySpring loadedN/ACorrection collarN/ARemarks (Correction collar)V/AIrisN/ACorrection level of chromatic aberrationExtended Apochromat (XAPO)Parfocalizing distance [mm]45Back focal plane (BFP) position [mm]-19.1Type of screw threadW20.32×0.706 (RMS)Brightfield (Reflected)N/ADarkfield (Transmitted)GoodDarkfield (Transmitted)KADIC (Reflected)N/APhase contrastN/AField formatic differentN/AMitteld (Transmitted)ExcellentMuter (Reflected)N/ADic (Reflected)N/AHase contrastN/AField formatice)N/AField formatice)N/AField formatice)N/AField formatice)N/AField formatice)N/AField formatice)N/AField formatite)ExcellentField formatice)N/AField format	Major application	Life Science
Working distance (WD) [mm]3.1Objective field number [mm]26.5Cover glass thickness [mm]0.17Immersion mediumAir/DrySpring loadedN/ACorrection collarN/ARemarks (Correction collar)N/AIrisN/ACorrection level of chromatic aberrationExtended Apochromat (XAPO)Parfocalizing distance [mm]45Back focal plane (BFP) position [mm]-19.1Type of screw threadW20.32×0.706 (RMS)Brightfield (Reflected)N/ADarkfield (Transmitted)ExcellentDarkfield (Transmitted)KodDIC (Reflected)N/APhase contrastN/ARelief contrastN/A	Magnification [X]	10
Objective field number [mm]26.5Cover glass thickness [mm]0.17Immersion mediumAir/DrySpring loadedN/ACorrection collarN/ARemarks (Correction collar)N/AIrisN/ACorrection level of chromatic aberrationExtended Apochromat (XAPO)Parfocalizing distance [mm]45Back focal plane (BFP) position [mm]-19.1Type of screw threadW20.32×0.706 (RMS)Brightfield (Reflected)N/ADarkfield (Reflected)N/ADarkfield (Reflected)N/ADic (Reflected)N/ADic (Reflected)N/ADic (Reflected)N/AParfocalizing distance [mm]ExcellentBrightfield (Transmitted)ExcellentDic (Reflected)N/ADic (Reflected)N/ABightfield (Transmitted)ExcellentDic (Reflected)N/AParfocalizing distanceN/A	Numerical aperture (NA)	0.4
Cover glass thickness [mm]0.17Immersion mediumAir/DrySpring loadedN/ACorrection collarN/ACorrection collarN/ARemarks (Correction collar)N/AIrisN/ACorrection level of chromatic aberrationExtended Apochromat (XAPO)Parfocalizing distance [mm]45Back focal plane (BFP) position [mm]-19.1Type of screw threadW20.32×0.706 (RMS)Brightfield (Reflected)N/ADarkfield (Reflected)N/ADarkfield (Reflected)N/ADIC (Reflected)N/APhase contrastN/A	Working distance (WD) [mm]	3.1
Immersion mediumAir/DrySpring loadedN/ACorrection collarN/ARemarks (Correction collar)N/AIrisN/ACorrection level of chromatic aberrationExtended Apochromat (XAPO)Parfocalizing distance [mm]45Back focal plane (BFP) position [mm]-19.1Type of screw threadW20.32×0.706 (RMS)Brightfield (Reflected)N/ADarkfield (Reflected)N/ADarkfield (Reflected)N/ADic (Reflected)N/ADIC (Reflected)N/APhase contrastN/ARelief contrastN/A	Objective field number [mm]	26.5
Spring loadedN/ACorrection collarN/ARemarks (Correction collar)N/AIrisN/ACorrection level of chromatic aberrationExtended Apochromat (XAPO)Parfocalizing distance [mm]45Back focal plane (BFP) position [mm]-19.1Type of screw threadW20.32×0.706 (RMS)Brightfield (Reflected)N/ADarkfield (Reflected)N/ADarkfield (Reflected)N/ADarkfield (Reflected)N/ADarkfield (Transmitted)GoodDIC (Reflected)N/APhase contrastN/ARelief contrastN/A	Cover glass thickness [mm]	0.17
Correction collarN/ARemarks (Correction collar)IrisN/ACorrection level of chromatic aberrationExtended Apochromat (XAPO)Parfocalizing distance [mm]45Back focal plane (BFP) position [mm]-19.1Type of screw threadW20.32×0.706 (RMS)Brightfield (Reflected)N/ADarkfield (Reflected)N/ADarkfield (Reflected)ScellentDarkfield (Reflected)N/ADarkfield (Transmitted)GoodDIC (Reflected)N/APhase contrastN/A	Immersion medium	Air/Dry
Remarks (Correction collar)IrisN/ACorrection level of chromatic aberrationExtended Apochromat (XAPO)Parfocalizing distance [mm]45Back focal plane (BFP) position [mm]-19.1Type of screw threadW20.32×0.706 (RMS)Brightfield (Reflected)N/ABrightfield (Transmitted)ExcellentDarkfield (Reflected)N/ADarkfield (Transmitted)GoodDIC (Reflected)N/APhase contrastN/ARelief contrastN/A	Spring loaded	N/A
IrisN/ACorrection level of chromatic aberrationExtended Apochromat (XAPO)Parfocalizing distance [mm]45Back focal plane (BFP) position [mm]-19.1Type of screw threadW20.32×0.706 (RMS)Brightfield (Reflected)N/ABrightfield (Reflected)N/ADarkfield (Reflected)N/ADarkfield (Reflected)ScellentDic (Reflected)N/APhase contrastN/ARelief contrastN/A	Correction collar	N/A
Correction level of chromatic aberrationExtended Apochromat (XAPO)Parfocalizing distance [mm]45Back focal plane (BFP) position [mm]-19.1Type of screw threadW20.32×0.706 (RMS)Brightfield (Reflected)N/ABrightfield (Reflected)N/ADarkfield (Reflected)N/ADarkfield (Reflected)M/ADic (Reflected)N/ADic (Reflected)N/APhase contrastN/ARelief contrastN/A	Remarks (Correction collar)	
Parfocalizing distance [mm]45Back focal plane (BFP) position [mm]-19.1Type of screw threadW20.32×0.706 (RMS)Brightfield (Reflected)N/ABrightfield (Transmitted)ExcellentDarkfield (Reflected)N/ADarkfield (Reflected)N/ADic (Reflected)N/ADic (Reflected)N/APhase contrastN/ARelief contrastN/A	Iris	N/A
Back focal plane (BFP) position [mm]-19.1Type of screw threadW20.32×0.706 (RMS)Brightfield (Reflected)N/ABrightfield (Transmitted)ExcellentDarkfield (Reflected)N/ADarkfield (Transmitted)GoodDIC (Reflected)N/ADIC (Reflected)N/APhase contrastN/ARelief contrastN/A	Correction level of chromatic aberration	Extended Apochromat (XAPO)
Type of screw threadW20.32×0.706 (RMS)Brightfield (Reflected)N/ABrightfield (Transmitted)ExcellentDarkfield (Reflected)N/ADarkfield (Transmitted)GoodDIC (Reflected)N/ADIC (Transmitted)ExcellentPhase contrastN/ARelief contrastN/A	Parfocalizing distance [mm]	45
Brightfield (Reflected)N/ABrightfield (Transmitted)ExcellentDarkfield (Reflected)N/ADarkfield (Transmitted)GoodDIC (Reflected)N/ADIC (Transmitted)ExcellentPhase contrastN/ARelief contrastN/A	Back focal plane (BFP) position [mm]	-19.1
Brightfield (Transmitted)ExcellentDarkfield (Reflected)N/ADarkfield (Transmitted)GoodDIC (Reflected)N/ADIC (Transmitted)ExcellentPhase contrastN/ARelief contrastN/A	Type of screw thread	W20.32×0.706 (RMS)
Darkfield (Reflected)N/ADarkfield (Transmitted)GoodDIC (Reflected)N/ADIC (Transmitted)ExcellentPhase contrastN/ARelief contrastN/A	Brightfield (Reflected)	N/A
Darkfield (Transmitted)GoodDIC (Reflected)N/ADIC (Transmitted)ExcellentPhase contrastN/ARelief contrastN/A	Brightfield (Transmitted)	Excellent
DIC (Reflected)N/ADIC (Transmitted)ExcellentPhase contrastN/ARelief contrastN/A	Darkfield (Reflected)	N/A
DIC (Transmitted)ExcellentPhase contrastN/ARelief contrastN/A	Darkfield (Transmitted)	Good
Phase contrast N/A Relief contrast N/A	DIC (Reflected)	N/A
Relief contrast N/A	DIC (Transmitted)	Excellent
	Phase contrast	N/A
Polarization Good	Relief contrast	N/A
	Polarization	Good

Last updated: Jan 21 2022 Specifications, design and accessories are subject to change without any notice or obligation on the part of the manufacturer.



Data Sheet

UPLXAPO10X

Fluorescence (B, G excitation)	Excellent
UV fluorescence (at 365 nm)	Excellent
Multiphoton	N/A
TIRF	N/A
IR	N/A
WLI	N/A
Auto focus	Yes
Product number	N5701900
UPC code	1-UXB190

Last updated: Jan 21 2022

Specifications, design and accessories are subject to change without any notice or obligation on the part of the manufacturer.