



Polaris semi-micro and analytical balances combine a brightly illuminated weighing chamber with advanced connectivity options for streamlined GLP-compliant recordkeeping and communication. Their multi-line display provides clear, step-by-step guidance, rapid weighing results and real-time application status for complete operational clarity. Checkweighing is made more efficient by a colour-changing backlight that instantly indicates whether samples fall within user-defined limits.

Polaris provides complete clarity in weighing - from its brightly-lit chamber to the expansive LCD display.







Features

- Solid, durable ABS housing to withstand daily use
- Grade 304 stainless steel pan allows easy cleaning
- Bright, LED-lit weighing chamber for clear visibility of samples
- Intuitive, easy-to-use display showing instructions, results and application status at a glance
- Colour-changing backlight in checkweighing mode to show if under, over or within acceptable limits
- Multilingual display allows use in many different countries
- Unique air diversion channel (ADT) below the weighing pan discharges warm air from the weighing chamber for more accurate weighing results (PAB 125i only)
- Selectable digital filtering helps minimise effects of vibration and disturbances
- Connect seamlessly to PCs, printers, or LIMS via Bluetooth®, RJ45 Ethernet, RS-232 and USB interfaces
- Compliance with Good Laboratory Practices (GLP) and Good Manufacturing Practices (GMP) standards for data tracking
- Up to 200 ingredients can be stored in the internal memory (10 formulations each holding 20 ingredients)
- · Security slot for optional lock and cable to help prevent theft
- Multi-level security permissions: 1 administrator plus up to 99 operators
- In-use cover and weigh-below hook provided with each model

Applications

- Weighing
- Parts counting
- Percentage weighing
- Checkweighing
- Check counting
- Display hold
- · Dynamic / animal weighing
- · Density determination
- Formulation
- Accumulation

About Adam:

For over 50 years, professionals worldwide have relied on Adam Equipment for an extensive selection of dependable and affordable weighing equipment. Adam provides the right balance of speed, performance and value.



Product Details

Model	PAB 125i	PAB 124i/e	PAB 224i/e	PAB 324i/e	PAB 424i/e
Capacity	80g/120g	120g	220g	320g	420g
Readability	0.00001g/0.0001g	0.0001g			
Pan Size	3.1" / 80mm ø				
Weighing Units	g, mg, ct, dwt, gr, oz, dr, tl.HK, tl.S, tl.T, mm, tol, tk, N, custom unit				
Stabilisation Time (sec)	3/5	3			
Interface	RJ45 Ethernet, Bluetooth®, RS-232, USB x2				
Calibration	Internal (Suffix 'i'), External (Suffix 'e')				
Display	7.4" Multi-Colour Backlit LCD				
Display Languages	English, German, French, Spanish, Portuguese, Italian				
Power Supply	18VDC 830mA adapter				
Housing	ABS plastic with glass draft shield				
Overall Dimensions	9.3"x15.7"x13.2" / 235x398x336mm				
Draft Shield Dimensions	7.6"x8.6"x9.6" / 193x218x243mm				
Net Weight	14.8lb / 6.7kg	13.9lb / 6.3kg ('e')	/ 14.5lb / 6.6kg ('i')	13.9lb / 6.3kg ('e')	/ 14.8lb / 6.7kg ('i')

Accessories

Item NumberDescription				
700100410	ABI-1 Ioniser			
600002028	AdamDU Data Collection Program			
3014011014	RS-232 cable 9M-9F			
3074010267	USB cable A-B			
3014016565	USB cable A-A			
700100046	Security Lock and Cable			
700660290	Calibration certificate			
3126011263	ATP2 Thermal Printer Paper			
3126011281	ATP2 Thermal Printer Paper (pack of 10)			

In The Box

Polaris PAB models are supplied with:

Glass draft shield (requires assembly)

Assembly tool

Weigh-below hook

In-use cover

Draft shield assembly instructions

Key Accessories



AVT Anti-Vibration Table

Ergonomically styled, the AVT offers a solid, stable surface developed specifically to help decrease vibration during measurement. Its large, scratch-resistant dark granite slab sits on shock-absorbing rubber mounts, while leveling feet accommodate uneven surfaces.



ATP2 Thermal Printer

The ATP2 is a compact general purpose thermal roll printer that connects via RS-232 interface to Adam scales and balances.



Adam Equipment follows a policy of continuous improvement and reserves the right to change specification and pricing without notice. Adam Equipment's standard terms and conditions of sale apply, Errors and omissions excepted.