

# **Petite Fleur-eo**



Refrigerated Heating Circulator with air-cooled refrigerating unit. Powerful, variable speed pump, housing of stainless steel, CFC and H-CFC free. Speed controlled pump (soft start), pump pressure control. With adjustable overtemperature protection according to DIN 12876.

## Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

## further functions:

E-grade Professional installed as standard, TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 10 programs (max. 100 steps), ramp function (linear and non-linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K, integrated technical glossary, 2nd set point, user menus (Administrator level), calendar start, wallpaper selection.

4-year warranty - registration required.

### Please note:

The machine is developed exclusively for external open operation, and does not possess an expansion tank. The filling of the thermofluid, and allowance for the temperature dependent volume changes is only possible via an externally connected application.

## Technical data according to DIN 12876

Operating temperature range	-40200 °C	
Temperature stability at -10°C	0,01 K	
temperature set point / display	5,7" colour Touchscreen	
Resolution of display	0,01 K	
Internal temperature sensor	Pt100	
Sensor external connection	Pt100	
nterface digital	Ethernet, USB (Host u. Device), RS232	
digital input	ECS ONE	and the second se
digital output	POKO ONE	patte feur Ann
Alarm message	optic, acoustic, relay	Tout
Safety classification	III / FL	3 2 2
Heating power	1,5 kW	and the second se
Cooling power with	Thermooil	
at 200°C	0,48 kW	-
at 150°C	0,48 kW	militar
at 100°C	0,48 kW	
at 50°C	0,48 kW	
at 20°C	0,48 kW	
Cooling power with	Ethanol	Order-No.: 1030.0012.01
at 0°C	0,45 kW	
at -20°C	0,27 kW	
at -30°C	0,16 kW	
at -40°C	0,04 kW	
Refrigeration machine	air-cooled, natural refrigerant	
Refrigerant (ASHRAE, GHS)	R290 (A3, H220)	
Refrigerant quantity	0,08 kg	
Gas warning sensor	without	
Circulation pump:		
nax. delivery	25 l/min	
nax. delivery pressure	0,9 bar	
Pump connection	M16x1 male	
max. permissible kin. viscosity	50 mm²/s	

## Technical data according to DIN 12876

min. filling capacity	21
Overall dimensions WxDxH **	260x450x504 mm
Net weight	45 kg
sound pressure level +/- 4 dB(A)	58 dB(A)
Power supply requirement	110-120V 1~ 60Hz
max. current	14 A
min. Fuse	10A
max. Fuse	16A
Pressure equipment category	4.3 PED
Degree of Protection	IP20
min. ambient temperature	5 °C
max. ambient temperature	40 °C

#### from Serial-No.:

1.1/17

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Accessories and periphery: mini-USB cable #54949\*, E-grade "Professional" #9496\*, E-grade "Explore" #10495, Adapter nom. dia. 12\*, sleeve nuts M16x1 male\*, Com.G@te Namur

\* standard equipment

Output data valid for: Room temperature 20°C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid: Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2% Example -5% voltage and + 2% frequency -> not allowed! -5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility: Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)

2. Three-phase devices with current consumption less than 63A --> with cable, without plug

3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at www.huber-online.com