

# **Grande Fleur-eo**



Refrigerated Heating Circulator with air-cooled refrigerating unit. Powerful, variable speed pump, housing of stainless steel, CFC and H-CFC free. Speed controlled pump (soft start), pump pressure control. With adjustable overtemperature protection according to DIN 12876.

### Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

#### further functions:

E-grade Professional installed as standard, TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 10 programs (max. 100 steps), ramp function (linear and non-linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K, integrated technical glossary, 2nd set point, user menus (Administrator level), calendar start, wallpaper selection.

4-year warranty - registration required.

#### Please note:

The machine is developed exclusively for external open operation, and does not possess an expansion tank. The filling of the thermofluid, and allowance for the temperature dependent volume changes is only possible via an externally connected application.

## Technical data according to DIN 12876

Operating temperature range Temperature stability at -10°C temperature set point / display Resolution of display Internal temperature sensor Sensor external connection

Interface digital

digital input digital output Alarm message Safety classification Heating power Cooling power with

at 200°C at 150°C at 100°C at 50°C at 20°C Cooling power with

at 0°C at -20°C at -30°C at -40°C

Refrigeration machine

Refrigerant (ASHRAE, GHS) Refrigerant quantity Gas warning sensor Circulation pump: max. delivery max. delivery pressure

Pump connection max. permissible kin. viscosity

-40...200 °C 0.01 K

5,7" colour Touchscreen

0,01 K Pt100 Pt100

Ethernet, USB (Host u. Device), RS232 ECS ONE

POKO ONE

optic, acoustic, relay

III / FL 1,5 kW Thermooil 0,6 kW 0,6 kW 0,6 kW 0,6 kW 0,6 kW Ethanol 0,6 kW 0,2 kW 0,2 kW

air-cooled, natural refrigerant R290 (A3, H220) 0,099 kg

47 l/min 0,9 bar M24x1,5 male 50 mm<sup>2</sup>/s

without



Order-No.: 1041.0005.01

### Technical data according to DIN 12876

min. filling capacity	1,5	
Overall dimensions WxDxH **	295x530x570 mm	
Net weight	53 kg	
Power supply requirement	110-120V 1~ 60Hz	
max. current	15 A	
Fuse	16 A	
Pressure equipment category	4.3 PED	
Degree of Protection	IP20	
min. ambient temperature	5 °C	
max. ambient temperature	40 °C	

1.1/20 from Serial-No.:

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

#### Included Accessories:

mini-USB cable #54949, E-grade "Professional" #9496, Adaptor M16x1 male to M24x1,5 female,

### Optional accessories:

E-grade "Explore" #10495, external sensor, temperature control / - connection hoses, thermofluids, SpyLight-Software, Com.G@te, further accessories, etc.: see catalog.

Note: Pump connections: Bore shape Y (60°) according to DIN 3863, pipework/flexible tempering hoses: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

Output data valid for: Room temperature 20°C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

-5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

### Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

- 1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
- 2. Three-phase devices with current consumption less than 63A --> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau SF Werner-von-Siemens-Str 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com