



The Cooling Bath are water baths with air-cooled refrigerating unit. Housing and tank of stainless steel. The refrigerating unit works continiously.

Together with the immersion thermostats can the cooling baths be used up to 200°C.

Technical data according to DIN 12876

from Serial-No.:	506700	1.0/22
max. ambient temperature	40 °C	
min. ambient temperature	5 °C	
max. Fuse	16A	
min. Fuse	10A	
max. current	2,6 A	
Power supply requirement	110-120V 1~ 50/60Hz	
Net weight	25 kg	Order-No.: 2009.0033.00
Overall dimensions WxDxH **	350x560x263 mm	
Width bath opening WxD/ bath depth	290x320/ 150 mm	-
Bath volume	12	
Gas warning sensor	without	Bular +
Refrigerant quantity	0,041 kg	
Kältemittel (ASHRAE, GSH)	R290 (A3, H220)	
Refrigeration machine	air-cooled, natural refrigerant	-
at -30°C	0,05 kW	
at -10°C	0,12 kW	
at 0°C	0,2 kW	
at 20°C	0,25 kW	
Cooling power		
Operating temperature range	-20200 °C	

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

Drain valve with cap #6839, adjustable base #40763, trolley , test tube racks Typ 1-4, Bath covers in various versions: see catalogue.

Output data valid for: Room temperature 20°C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid: Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2% Example -5% voltage and + 2% frequency -> not allowed! -5% voltage and - 2% frequency -> allowed

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)

2. Three-phase devices with current consumption less than 63A --> with cable, without plug

3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

** Please respect space requirements. See operating conditions at www.huber-online.com