# huber

# **Unichiller 017T-H**

Chiller with air-cooled refrigerating unit and circulation pump (stainless steel). Housing, atmospheric open expansion tank and copper soldered evaporator made of stainless steel. With digital level indicator. With adjustable overtemperature protection according to DIN 12876. For externally closed applications.

#### Pilot ONF:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

4-year warranty - registration required.

## Technical data according to DIN 12876

Operating temperature range temperature set point / display Internal temperature sensor Sensor external connection Interface digital

Temperature stability at -10°C

Safety classification Heating power Cooling power at 15°C at 0°C

at -10°C Refrigeration machine

Refrigerant (ASHRAE, GHS)

Circulation pump: max. delivery

max. delivery pressure Delivery at 0,12 bar Delivery at 0,5 bar Delivery at 1,0 bar Delivery at 1,5 bar Delivery at 2,0 bar Delivery at 2,5 bar Delivery at 3,0 bar Pump connection min. filling capacity

Volume of expansion

Overall dimensions WxDxH \*\* sound pressure level +/- 4 dB(A) Power supply requirement

Degree of Protection min. ambient temperature max. ambient temperature

Pressure equipment category

-10...100 °C

5,7" colour Touchscreen

Pt100 Pt100

Ethernet, USB (Host u. Device), RS232

0,2 K III / FL 2 kW

1,7 kW 0.9 kW

0,4 kW

air-cooled, CFC- and

HCFC-free R449A (A1, H280)

В

30 l/min 3,8 bar 29 l/min 25 l/min 21 l/min 17 l/min 13,5 l/min 10 l/min 6,5 l/min G3/4 male

2,5 l

450x510x1231 mm

64 dB(A) 208V 2~ 60Hz 4.3 PED IP20 5 °C 40 °C



Order-No.: 3013.0074.01

from Serial-No.: 1.0/21

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original. Included Accessories:

mini-USB cable #54949, cover expansion vessel, Hose coupling for G3/4 male,

### Optional accessories:

Com.G@te, external sensor, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20°C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

xample -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

- 1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
- 2. Three-phase devices with current consumption less than 63A --> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau SE Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com