## huber

## **Unichiller 040T**

Chiller with air-cooled refrigerating unit and circulation pump (stainless steel). Housing, atmospheric open expansion tank and copper soldered evaporator made of stainless steel. With digital level indicator. For externally closed applications.

## Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

4-year warranty - registration required.

## Technical data according to DIN 12876

Operating temperature range -10...40 °C 5.7" colour Touchscreen temperature set point / display Internal temperature sensor Pt100 Order-No.: 3014.0053.01 Pt100 Sensor external connection Ethernet, USB (Host u. Interface digital Device), RS232 Temperature stability at -10°C 0.5 K Safety classification I / NFL Cooling power at 15°C 4 kW at 0°C 2,5 kW at -10°C 1,1 kW Refrigeration machine air-cooled. CFC- and **HCFC-free** Refrigerant (ASHRAE, GHS) R449A (A1, H280) Circulation pump: max. delivery 31 l/min max. delivery pressure 4 har Delivery at 0,5 bar 27 I/min Delivery at 1,0 bar 22 I/min Delivery at 1,5 bar 19 I/min Delivery at 2.0 bar 16 l/min Delivery at 2,5 bar 12 I/min 8 I/min Delivery at 3,0 bar Delivery at 3,5 bar 5 l/min Pump connection G3/4 male min. filling capacity 3.5 I Volume of expansion Overall dimensions WxDxH \*\* 500x552x1451 mm Net weight 166 kg sound pressure level +/- 4 dB(A) 69 dB(A) Power supply (3 Phase) 460V 3~ 60Hz Pressure equipment category 4.3 PED Degree of Protection IP20 min. ambient temperature 5°C 40 °C max. ambient temperature

from Serial-No.: 1.0/19

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original. Included Accessories:

mini-USB cable #54949, cover expansion vessel, Hose coupling for G3/4 male,

Optional accessories:

Com.G@te, external sensor, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20°C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility: Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

- 1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
- 2. Three-phase devices with current consumption less than 63A --> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau SE Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com