

# **Unichiller 160T**

Chiller with air-cooled refrigerating unit and circulation pump (stainless steel). Housing, atmospheric open expansion tank and copper soldered evaporator made of stainless steel. With digital level indicator. For externally closed applications.

### Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

4-year warranty - registration required.

# Technical data according to DIN 12876

Operating temperature range temperature set point / display Internal temperature sensor Sensor external connection Interface digital	-1040 °C 5,7" colour Touchscreen Pt100 Pt100 Ethernet, USB (Host u. Device), RS232	
Temperature stability at -10°C	0,5 K	
Safety classification	I/NFL	n isker
Cooling power	.,	
at 15°C	16 kW	
at 0°C		
	8,8 kW	
at -10°C	4 kW	
Refrigeration machine	air-cooled, CFC- and HCFC-free	
Defrigement (ACUDAE CUC)		- = Unichiller 🧧
Refrigerant (ASHRAE, GHS)	R449A (A1, H280)	Chieffinier C
Circulation pump:	C3	
max. delivery	96 l/min	and the second s
max. delivery pressure	6,4 bar	
Delivery at 1,0 bar	65 l/min	
Delivery at 2,0 bar	60 l/min	
Delivery at 2,5 bar	45 l/min	
Delivery at 3,0 bar	40 l/min	
Delivery at 4,0 bar	25 l/min	
Pump connection	G1 1/4 male	
min. filling capacity	14 I	
Volume of expansion	39	L T
Overall dimensions WxDxH **	904x1582x1837 mm	6
Power supply (3 Phase)	460V 3~ 60Hz	0. I N
Pressure equipment category	I	Order-No.: 3056.0003.01
Degree of Protection	IP20	
min. ambient temperature	5 °C	
max. ambient temperature	40 °C	

### from Serial-No.:

1.0/20

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original. Accessories and periphery: mini-USB cable #54949\*, Hose coupling for G1 1/4 male\*, , cover expansion tank\*, connection tubes, external sensor, connecting cable

# Technical data according to DIN 12876

#### \* standard equipment

Output data valid for: Room temperature 20°C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid: Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2% Example -5% voltage and + 2% frequency -> not allowed! -5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility: Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)

2. Three-phase devices with current consumption less than 63A --> with cable, without plug

3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at www.huber-online.com