huber

Unichiller 260Tw

Chiller with water-cooled refrigerating unit and circulation pump (stainless steel). Housing, atmospheric open expansion tank and copper soldered evaporator made of stainless steel. With digital level indicator. For externally closed applications.

Pilot ONE

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

4-year warranty - registration required.

Technical data according to DIN 12876

Operating temperature range	-2040 °C		
temperature set point / display	5,7" colour Touchscreen		
Internal temperature sensor	Pt100	Order-No.:	3058.0007.01
Sensor external connection	Pt100		
Temperature stability at -10°C	0,5 K		
Interface digital	Ethernet, USB (Host u. Device), RS232		
Safety classification	I / NFL		
Cooling power			
at 15°C	26 kW		
at 0°C	26 kW		
at -10°C	18 kW		
at -20°C	12 kW		
Refrigeration machine	water-cooled, CFC- and HCFC-free		
Refrigerant (ASHRAE, GHS)	R449A (A1, H280)		
Circulation pump	D3		
max. delivery	210 l/min		
max. delivery pressure	4,7 bar		
Delivery at 1,1 bar	202 l/min		
Delivery at 1,5 bar	193 l/min		
Delivery at 2,0 bar	179 l/min		
Delivery at 2,5 bar	159 l/min		
Delivery at 3,0 bar	140 l/min		
Delivery at 3,5 bar	115 l/min		
Delivery at 4,0 bar	77 l/min		
Delivery at 4,5 bar	31 l/min		
Pump connection	G1 1/4 male		
Cooling water connection	G3/4 male		
min. cooling water differential pressure	1 bar		
max. cooling water pressure	6 bar		
min. filling capacity	15 I		
Volume of expansion	22		
Overall dimensions WxDxH **	760x800x1615 mm		
Power supply (3 Phase)	460V 3~ 60Hz		
Pressure equipment category	1		
Degree of Protection	IP20		

Technical data according to DIN 12876

min. ambient temperature	5 °C	
max. ambient temperature	40 °C	

from Serial-No.: 1.0/20

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

mini-USB cable #54949, cover expansion vessel, Hose coupling for G1 1/4 male, hose coupling cooling water for G3/4 male

Optional accessories:

Com.G@te, external sensor, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20°C, cooling water inlet 15°C and 1 bar differential pressure between cooling water inlet and outlet. This temperature control unit has been designed to operate with cooling water up to 20°C. As the cooling water temperature increases, drop in the cooling power should be expected, and also an increased cooling water flow rate possible. Materiels used in the cooling water circuit include; copper, Stainless steel 1.4401, MS, PA, PPE, PTFE and EPDM. Please use suitable cooling water.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility: Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

- 1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
- 2. Three-phase devices with current consumption less than 63A --> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

** Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau SE Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com