# huber

# HTS 3

Heat Exchanger Unit with circulation pump (industrial plastic material). Housing, atmospheric open expansion tank and external plate heat exchanger (copper soldered), made of stainless steel. With digital level indicator. For externally closed applications.

#### Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

4-year warranty - registration required.

## Technical data according to DIN 12876

Operating temperature range ( secondary side ) (3)...(95) °C Temperature stability 0.1 K temperature set point / display 5,7" colour Touchscreen Internal temperature sensor Pt100 Pt100 Sensor external connection Ethernet, USB (Host u. Interface digital Device), RS232 Alarm message optic, acoustic, relay I / NFL Safety classification Water

Cooling power with Wate at 20°C 3 kW
Circulation pump Imme

Circulation pump Immersion pump max. delivery 33 l/min max. delivery pressure 0,7 bar

Pump connection M16x1 male max. permissible kin. viscosity 50 mm²/s
Cooling water connection G1/2 male

Consumption at water 10°C, flow 20°C

min. cooling water differential pressure

max. cooling water pressure

min. filling capacity

450 l/h

2 bar

6 bar

3,5 l

Volume of expansion 4,5 I
Overall dimensions WxDxH \*\* 280x491x414 mm

Net weight 21 kg

Power supply requirement 200-240V 1~/2~ 50/60Hz

max. current

min. Fuse

max. Fuse

16A

Degree of Protection

min. ambient temperature

max. ambient temperature

40 °C

Mark Transfer Station

Order-No.: 3069.0001.01

from Serial-No.: 398904 1.0/20

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original. Included Accessories:

### Technical data according to DIN 12876

Optional accessories:

Com.G@te, temperature control / - connection hoses, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20°C, cooling water inlet 10°C and 2 bar differential pressure between cooling water inlet and outlet. This temperature control unit has been designed to operate with cooling water up to 20°C. Materiels used in the cooling water circuit include; copper, Stainless steel 1.4401, MS, PA, PPE, PTFE and EPDM. Please use suitable cooling water.

In accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 10%, as long as the frequency tolerance does not run in the opposite direction.

Example: -10% voltage and + 3% frequency -> not allowed!

-10% voltage and -3% frequency -> allowed.

Information to Electromagnetic compatibility: Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

- 1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
- 2. Three-phase devices with current consumption less than 63A --> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

Special Case: Acetone and Polyglycol: The plastic pump is not resistant against acetone and polyglycols (depending on the manufacturer). It is recommended that water is mixed with either glysantine or ethylene glycol for freeze protection. A more resistant plastic is available on request at an additional cost.

\*\* Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau SE Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com