

## Flow Control Cube MID

Flow Control Cube MID (Magnetic-Inductive Flowmeter) is used to measure and control the flow and pressure of the thermal fluid and can only be used in conjunction with Huber temperature control systems with Pilot ONE.

The flow measurement is made magnetic-inductive flow meter. Only electrically conductive thermofluids can be measured and controlled. All wetted parts made of stainless steel / plastic (PTFE).

The control unit consists of the following:

Housing, flow meter, VPC bypass, internal pressure sensor in flow, connection for external pressure sensor (flow), DEM module, CAN switch, complete wiring and piping (insulated), power supply 90-240V  $1 \sim /2 \sim 50/60$ Hz Schuko plug.

## Technical data according to DIN 12876

Operating temperature range

min. volume flow max. volume flow max. volume pressure Accuracy flow control

Overall dimensions WxDxH \*\* sound pressure level +/- 4 dB(A)

fluid connection

Power supply requirement

max. current Fuse

Degree of Protection min. ambient temperature max. ambient temperature -40...130 °C

0,2 l/min

80 l/min

6 bar

+/- 0,1 l/min

420x593x591 mm

43 dB(A)

M38x1,5 male

90-240V 1~/2~ 50/60Hz

0,2 A 2 A

IP20

5°C

40 °C



Order-No.: 3601.0006.00

from Serial-No.: 550864 1.0/24

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

roller set #10894

Optional accessories:

Adaptor, temperature control / -connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20°C

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

- 1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
- 2. Three-phase devices with current consumption less than 63A --> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau SE Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com