# huber

# **Unimotive 20w**

Refrigerated Heating Circulator with water-cooled cooling machine and electronical level indicator. Magnetic coupled circulation pump made of stainless steel. Automatical switch-over and capacity adaption for heating and cooling machine. Copper soldered evaporator, moistened parts and housing made of stainless steel. As well as for externally closed and also externally open applications. With adjustable overtemperature protection according to DIN 12876. Optional pump pressure control via controlled bypass.

The Unimotive model series is specially designed for applications in the automotive industry. The temperature control systems are constructed for operation with Water-ethylene glycol mixture incl. corrosion protection (for example Glysantin®) down to -45° C. Typical applications include temperature simulations as well as material testing and temperature-dependent stress and load tests for automotive parts and functional components. The optionally available "Flow Control Cube" enables precise flow rate measurement and control.

Information on the temperature-dependent pressure sand flowrates rate with various thermal fluids can be found at www.huber-online.com

#### Pilot ONF:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

## further functions:

max. delivery pressure

Peter Huber Kältemaschinenbau SF

Delivery at 1,0 bar

E-grade Professional installed as standard, TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 10 programs (max. 100 steps), ramp function (linear and non-linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K, integrated technical glossary, 2nd set point, user menus (Administrator level), calendar start, wallpaper selection.

5,3 bar

179 I/min

D-77656 Offenburg

Tel 0781/9603-0

Fax 0781/57211

www huber-online com

4-year warranty - registration required.

# Technical data according to DIN 12876

Operating temperature range	-4595 °C
Temperature stability at -10°C	0,05 K
temperature set point / display	5,7" colour Touchscreen
Resolution of display	0,01 K
Internal temperature sensor	Pt100
Sensor external connection	Pt100
Interface digital	Ethernet, USB (Host u. Device), RS232
digital input	ECS ONE
digital output	POKO ONE
Alarm message	optic, acoustic, relay
Safety classification	III / FL
Heating power	12 kW
Cooling power with	Water/ Glysantin 40/60
at 20°C	21 kW
Cooling power with	Water/ Glysantin 40/60
at 0°C	17,5 kW
at -20°C	9,5 kW
at -30°C	5,5 kW
at -40°C	3 kW
Refrigeration machine	water-cooled, CFC- and HCFC-free
Refrigerant (ASHRAE, GHS)	R452A (A1, H280)
Refrigerant quantity	3,4 kg
Circulation pump:	MK pump
max. delivery	201 l/min

Werner-von-Siemens-Str 1

# Technical data according to DIN 12876

Delivery at 2,0 bar Delivery at 3,0 bar Delivery at 4,0 bar Delivery at 5,0 bar Pump connection

max. permissible kin. viscosity Cooling water connection

min. cooling water differential pressure max. cooling water differential pressure max. cooling water pressure max. System pressure min. filling capacity

Filling capacity expansion tank
Overall dimensions WxDxH \*\*

Power supply factory configured (3 Phase)

Degree of Protection min. ambient temperature max. ambient temperature 154 l/min 124 l/min 87 l/min 42 l/min M38x1,5 male 200 mm<sup>2</sup>/s G3/4 male

1 bar 4 bar 6 bar 6 bar 8,2 I 19,9 I

730x804x1738 mm

460V 3~ 60Hz

IP20 5 °C 40 °C



Order-No.: 5007.0005.01

from Serial-No.: 1.0/23

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

## Included Accessories:

mini-USB cable #54949, E-grade "Professional" #9496, Com.G@te DIGITAL, hose connection for G3/4 male,

## Optional accessories

E-grade "Explore" #10495, SpyLight-Software, Com.G@te PLUS, RS232 adapter cable #55018, Thermofluid, external pressure sensor, metal hoses, braided hoses for cooling water, VPC-Bypass, external sensor, connecting cable, isolation sleeve for external open applications, further accessories, etc.: see catalog.

Note: Pump connections: Bore shape Y  $(60^{\circ})$  according to DIN 3863, pipework/flexible tempering hoses: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

Output data valid for: Room temperature 20°C, cooling water inlet 15°C and 1 bar differential pressure between cooling water inlet and outlet. This temperature control unit has been designed to operate with cooling water up to 20°C. As the cooling water temperature increases, drop in the cooling power should be expected, and also an increased cooling water flow rate possible. Materiels used in the cooling water circuit include; copper, Stainless steel 1.4401, MS, PA, PPE, PTFE and EPDM. Please use suitable cooling water.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Attention: leakage current > 3,5mA

Standard delivery conditions - Power cable configuration:

- 1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
- 2. Three-phase devices with current consumption less than 63A --> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

Peter Huber Kältemaschinenbau SE Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com

# Technical data according to DIN 12876

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau SE Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com