





The RV 8 Rotary Evaporator is the manual basic model in the family of IKA Rotation Evaporators. It finds a multitude of uses in the chemical, pharmaceutical, and biotechnology industries, in research and development, in manufacturing and quality assurance, in laboratories, and in plant construction. Thanks to specially designed glass guides, the vertical coated condenser makes extremely efficient use of the 1500 cm² cooling surface. Digital displays for speed and heating bath temperature enable optimum control of all distillation processes.

- New: 4 I heating bath

- integrated safety lift-out function in case of power failure

www.ika.com Subject to technical changes



- package includes Woulff bottle
- water/oil heating bath with carrying handles
- locking button for fixing heating bath temperature
- clearly legible, glass-covered, black-and-white display panel
- locking mechanism: red indicator shows unlocked position of the vapor tube
- manual lift for precise positioning of the glassware
- adjustable immersion angle
- single-handed manual lift handling, suitable for left and right-handed operators
- speed range: 5 300 min-1
- low device voltage (24V) ensures user safety
- flask clamping mechanism with integrated push-off function for easy exchange of evaporation flasks
- high-efficiency condenser with 1500 cm² cooling surface low space requirements
- compatible with the entire range of IKA RV 10 glassware



Technical Data

vertical 1600 DC 5 - 300 ±1 ±1
DC 5 - 300 ±1
5 - 300 ±1
±1
±1
manual
120
room temp 180
1400
±1
4
510 x 490 x 345
26.07
5 - 40
80
IP 20
100 - 240
50/60
1500
24