



designed for scientists



## CAL-O-100

/// Data Sheet

With the certified standard silicon oil you are able to check the measurement accuracy of your ROTAVISC. The certificate is part of the delivery.

Standard silicon oils with different viscosities or temperature conditions can be ordered customer-specifically.



designed for scientists

### Technical Data

Viscosity Accuracy (FSR) [%]	1
Verification Temperature [°C]	25
Dynamic viscosity [mPa.s]	100
Useable volume max. [ml]	500
Period of validity (months)	12
Weight [kg]	0.8
Permissible ambient temperature [°C]	5 - 40

