

Nanodyne Replacement Illuminator for Nikon TE2000 - Included Items

PN 10589 Leica DMLB
100W Illuminator Assy

PN 11170 Pot-Cable Assy
(30 in long)

PN 10695 SHCS
M3 x 0.5 x 12 mm
(3 pcs)

PN 10718 Adapter
Nikon Optiphot-2

Additional Items Included But Not Shown:

PN 10490 Hex Key 5/64 inch (for securing illuminator to adapter)

PN 10566 Hex Key 2.5mm long arm ball end (for M3 SHCS to attach adapter to microscope)

The illuminator may be powered by plugging the cable into the power supply provided, or into a suitable USB port on a computer or other device.



PN 11163 Power Supply 5V 2.1A and
PN 10734 Power Cable 1.35mm
ID/3.5mm OD x USB A 6 ft.

Power supplies are subject to substitution without notice due to availability issues and changes in regulations.



PN 10736 Rubber plug to block
unused AC power recepticle.



3M VHB tape to secure pot cable

If Needed see the Nikon Optiphot-2 installation instructions for removing the original illuminator and attaching the Nanodyne one.

Wayne Bonin	12/10/2019	
PN 11278 Nikon TE2000 Illuminator System		REV 3
SHEET 1 OF 1		