



More information on the website
radwag.com/en/info,w1,7D8

XA 6/21.5Y.M.A Microbalance



XA 6/21.5Y.M.A Microbalance

The drawings, photos and graphics used are for illustrative purposes only.

Functions



Autotest



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



Newton unit
measurement



Statistics



Checkweighing



IR sensors



GLP Procedures



Animal weighing



Pipettes Calibration



Air density correction



Automatic sliding door



Density determination



Moveable range



Differential weighing



Ambient conditions
monitoring



Statistical Quality Control



Packaged Goods Control



ALIBI Memory



Wi-Fi

Datasheet

	XA 6/21.5Y.M.A Microbalance
Metrological parameters	
Maximum capacity [Max]	6/21 g
Minimum load	0,1 mg
Readability [d]	1/2 µg
Verification unit [e]	1 mg
Tare range	-21 g
Standard repeatability [5% Max]	1,3 µg
Standard repeatability [Max]	3,5 µg
Standard minimum weight (USP)	2,6 mg
Standard minimum weight (U=1%, k=2)	0,26 mg
Permissible repeatability [5% Max]	2 µg
Permissible repeatability [Max]	5 µg
Linearity	±9 µg
Eccentric load deviation	15 µg
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times \text{Rt}$
Stabilization time	~3,5 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatic - Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, weighing pan, weighing pan shield, power supply, brush, fabric dust cover.
Weighing chamber dimensions	199×170×217 mm
Weighing pan dimensions	ø30 mm
Packaging dimensions	750×492×595 mm
Net weight	14,5 kg
Gross weight	18,9 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3°C/1h (±1°C/8h)
Relative humidity	40% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

Accessories

MediaBox
RFID Tags
Antivibration Tables
Power Adapters
Protective cover for balances
RS 232, RS 485 cables
Additional modules
Anti-Draft Chamber for Microbalances
Professional Weighing Tables
Protective cover for balances
Barcode scanners
MICRO-KIT - Set of Holders for Microscale Glassware

Label Printers
THBR 2.0 System - Ambient Conditions Monitoring
RS 232, RS 485 cables
Adapters for Pipettes Calibration
Anti-Draft Chamber for XA 4Y and XA 5Y Balances
Weighing dishes
Antistatic ionizer
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter
Under-pan weighing

Software

E2R System
Label Editor R02
R-LAB
RADWAG Development Studio

RAD-KEY
RADWAG Remote Desktop
Scales Editor 2.1

Device dimensions

XA 6/21.5Y.M.A Microbalance

